

Unichiller 012

Chiller with air-cooled refrigerating unit and circulation pump. Evaporator (cooler), tank and housing of stainless steel. Pump made of industrial plastic material. Digital Temperature adjustment and digital temperature display. Level indicator with sight glass.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range temperature set point / display Internal temperature sensor Sensor external connection Temperature stability at -10°C

Interface digital

Safety classification

Cooling power at ambient temperature +20°C

at 15°C at 0°C at -10°C at -20°C

Refrigeration machine

Refrigerant (ASHRAE, GHS)

Refrigerant quantity Circulation pump: max. delivery max. delivery pressure

max. delivery pressur Delivery at 0,5 bar Pump connection min. filling capacity Volume of expansion

Overall dimensions WxDxH **

Net weight

sound pressure level +/- 4 dB(A) Power supply requirement

max. current
min. Fuse
max. Fuse
Degree of Protection

Degree of Protection min. ambient temperature max. ambient temperature -20...40 °C

5,7" colour Touchscreen

Pt100 Pt100 0,5 K

Ethernet, USB (Host u. Device), RS232

I / NFL

1,2 kW 1 kW 0,7 kW 0,25 kW

air-cooled, CFC- and HCFC-free R449A (A1, H280)

0,35 kg

Immersion pump

29 I/min 1 bar 21 I/min G3/4 male 3,8 I 1,7 I

420x487x579 mm 60 kg

208V 2~ 60Hz 6,5 A 2x10A 2x16A IP20 5 °C 40 °C

59 dB(A)



Order-No.: 3009.0153.01

from Serial-No.: 529441 1.2/23

Technical data according to DIN 12876

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

mini-USB cable #54949, cover expansion vessel, Hose coupling for G3/4 male,

Optional accessories:

Com.G@te, external sensor, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and +2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Special Case: Acetone and Polyglycol: The plastic pump is not resistant against acetone and polyglycols (depending on the manufacturer). It is recommended that water is mixed with either glysantine or ethylene glycol for freeze protection. A more resistant plastic is available on request at an additional cost.

Standard delivery conditions - Power cable configuration:

- 1. Single / two-phase devices (100V to 240V) --> with power cable and country-specific plug (please specify when ordering)
- 2. Three-phase devices with current consumption less than 63A --> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A --> without cable, without plug

This equipment is compliant to US-SNAP and all applicable EU laws. The US-SNAP end-use for this equipment is the industrial process refrigeration. Certification by a Notified Body upon request.

** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau SE Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com