# huber

# Ministat 125



Refrigerated Heating Circulator Bath with air-cooled cooling machine. Powerful, variable speed, pressure and suction pump, evaporator (cooler) and housing of stainless steel, CFC and H-CFC free. With adjustable overtemperature protection according to DIN 12876.

#### Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 11 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-1 warranty - registration required.

### Technical data according to DIN 12876

Operating temperature range Temperature stability at -10°C temperature set point / display Internal temperature sensor Sensor external connection

Interface digital

Safety classification Heating power Cooling power at 100°C at 20°C at 0°C at -10°C at -20°C

Refrigeration machine

Refrigerant Refrigerant quantity Gas warning sensor Pressure pump max. delivery max. delivery pressure

Suction numn

Suction pump

max. delivery (suction)

max. delivery pressure (suction)

Pump connection

max. permissible kin. viscosity

Bath volume min. filling capacity Bath capacity with displacement rack

Width bath opening WxD / bath depth

Overall dimensions WxDxH \*\*

Net weight

Power supply requirement

max. current

-25...150 °C 0.02 K

5,7" colour Touchscreen

Pt100 Pt100

Ethernet, USB (Host u. Device), RS232 Class III / FL

1 kW

0,3 kW 0,3 kW 0,21 kW 0,15 kW 0,05 kW

air-cooled, natural refrigerant

R290 0,066 kg without

27 l/min 0.7 bar yes 20 l/min 0.4 bar M16x1 male 50 mm²/s

2,75 l 2 l 1.3 l

178 x 80 / 120 mm 225x370x429 mm

25 kg

230V 1~ 50/60Hz

6 A



Order-No.: 2014.0011.01

## Technical data according to DIN 12876

from Serial-No.:	152933	1.0/12
min. ambient temperature	5 °C	
max. ambient temperature	35 °C	
Degree of Protection	IP20	
max. Fuse (1 phase)	16A	
min. Fuse (1 phase)	10A	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions.

Accessories and periphery: mini-USB cable #54949\*, Adapter nom. dia. 12 mm\*, dummy plugs\*, sleeve nuts thread M16x1\*, connection tubes, drain valve, displacement insert to reduce bath volume, calibration insert \* standard equipment

Output data valid for: Room temperature 20°C

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Peter Huber Kältemaschinenbau GmbH Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

<sup>\*\*</sup> Please respect space requirements. See operating conditions at www.huber-online.com