
GEM Meeting mechanics and services 08.02.2013

Quick connectors cooling water



This kind of connectors are used for the CMS drift tube muon chambers. But for Gas. So it was possible to use brass. We need stainless steel.

Barthel Philipps RWTH Aachen

GEM Meeting mechanics and services 08.02.2013

- -At the moment this quick connectors are only available with diameter 6mm.
- -Swagelok will check if its possible to get a 8mm version.
- Otherwise we have to use an Adapter or switch to an other supplier.

Types:

Male connector (bulkhead version): SS-QC4-D1-6M0 Price: 60,4 €

Female connector : SS-QC4-B-6M0 Price: 49,30€

Maximum water flow: 15 Liter/min. (cloud someone check if this is OK)

Barthel Philipps RWTH Aachen

GEM Meeting mechanics and services 08.02.2013

